

Strainer Screen Ordering Checklist

What Wodong needs to quote a screen, a basket, a temporary strainer or a sanitary core

Send the items below on WhatsApp or by email. A drawing or a sample photo covers all of them at once.

T Strainer Screens and Y Strainer Screens

- Material: stainless steel 304, 316, 316L, mild steel or another alloy
- Filtration construction: wire cloth only, simplex perforated, or perforated with a cloth liner
- Dimensions: outside diameter and length of the screen cylinder
- Filtration precision: mesh count from 2 mesh to 635 mesh, or hole size from 0.4mm up to 1 inch
- Material thickness

Strainer Baskets

- Material: stainless steel 304, 316 or 316L
- Filtration construction: simplex perforated, perforated with wire mesh liner, or wire mesh only
- Handle style and dimensions
- Basket bottom: perforated or blank cap
- Filtration range: wire cloth 8 mesh to 500 mesh, perforated 0.4mm to 1 inch

Temporary Pipeline Strainers

- Material: stainless steel 304 or 316
- Construction: temporary cone, temporary basket or temporary plate
- Dimensions of body, ring and handle (standard handle is 1 inch wide by 4 inch long)
- Filtration precision: standard grades 10, 20, 30, 40, 60, 80 and 100 mesh
- Material thickness

Sanitary Strainer Cores

- Perforated hole specification: 1/8 inch, 1/4 inch, 0.033 inch, 0.050 inch or other
- Wall thickness
- Inside diameter
- Length
- Surface treatment: electropolishing on 316 fluid contact surfaces

Send It To Us

WhatsApp +86 15931370444 | sales@ykmesh.com | TEL +86-318-7969611

CAD files are exchanged on request rather than published for download. All enquiries are replied within 24 hours.